

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190190052

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Avikrimp Quick Disconnect, Female, for 12-14 (3.30-2.00mm²) Wire, Box, Tab 6.35 x 0.81mm

- Documents:
- 3D Model (PDF)

Product Specification PS-19902-013-001 (PDF)
- 3D Model

Product Specification PS-19902-014-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-19902-011-001 (PDF)

Agency Certification

CSA

LR18689

UL

E79133

General

Product Family

Quick Disconnects

Series

19019

Crimp Quality Equipment

Yes

Insulated

Partial

Overview

Standard Quick-Disconnect Terminals

Product Name

Avikrimp

Taxonomy

Quick Disconnects

Type

Quick Disconnect

UPC

800753038561

Physical

Barrel Type

Closed

Color - Resin

Yellow

Flammability

94V-2

Gender

Female

Glow-Wire Capable

No

Insulation

Nylon (PA)

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

1.021/g

Orientation

Straight

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

6.35mm

Temperature Range - Operating

-65° to +105°C

Wire Insulation Diameter

4.30mm max.

Wire Size AWG

12, 14

Electrical

Voltage - Maximum

300V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

P-8142

Reference - Drawing Numbers



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19019 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640011800
Crimp Head for the AT-200 Pneumatic Hand Tool	640051800

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001,
PS-19902-014-001
SD-19019-001-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION