

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190340005**
Status: **Active**
Overview: Snap Plugs and Receptacles
Description: InsulKrimp Snap Plug, for 18-22 AWG Wire, 22.61mm Length

Documents:

3D Model (PDF)	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Quick Disconnects
Series	<u>19034</u>
Crimp Quality Equipment	Yes
Insulated	Partial
Overview	<u>Snap Plugs and Receptacles</u>
Product Name	InsulKrimp
Taxonomy	Quick Disconnects
Type	Snap Plug
UPC	800753047327

Physical

Barrel Type	Closed
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.158/g
Orientation	Straight
Packaging Type	Bag
Tab Thickness	N/A
Tab Width	N/A
Wire Insulation Diameter	3.60mm max.
Wire Size AWG	18, 20, 22

Electrical

Voltage - Maximum	600V
-------------------	------

Material Info

Engineering Number	A-269X
--------------------	--------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19034-004-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19034 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade	<u>640010100</u>
--------------	------------------

Hand Crimp Tool for Avikrimp and InsulKrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)

PremiumGrade	<u>640010300</u>
--------------	------------------

Hand Crimp Tool for InsulKrimp Terminals and Splices, 10-22

AWG (Rings,
Spades, Hooks,
Block Spades and
Flanged Spades)
Crimp Head for the 640050100
AT-200 Pneumatic
Hand Tool
Crimp Head for the 640050300
AT-200 Pneumatic
Hand Tool
ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION