

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191930152

Status:

Active

Overview:

VersaKrimp Terminals and Splices

Description:

VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6)

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19193

Crimp Quality Equipment

Yes

Overview

VersaKrimp Terminals and Splices

Product Name

VersaKrimp

Taxonomy

Ring and Spade Terminals

Type

Ring

UPC

800755049992

Physical

Barrel Type

Closed - Brazed

Insulation

None

Material - Plating Mating

Tin

Net Weight

2.939/g

Packaging Type

Bag

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Stud Size

1/4" (M6)

Termination Interface: Style

Crimp or Compression

Wire Size AWG

8

Wire Size mm²

6.60-10.50

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

D-350-14


Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19193-016-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19193 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Putt Pump Hydraulic System, Die set required	192860117
Die Set (large) for the HHLS Hydraulic Crimper	192900001
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	192940008
Hydraulic Dieless Crimping Tool	638161700

PremiumGrade Hand	<u>640013900</u>
Crimp Tool for 2-8	
AWG Terminals	
RHT1080 Hand	<u>640034400</u>
Crimp Tool	
Square “DIN” style	<u>640037670</u>
dies for 8 AWG	
Crimp Head for the	<u>640074400</u>
AT-200 Pneumatic	
Hand Tool	

This document was generated on 01/31/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION