

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190690241

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 3/8" (M9), Length 26.82mm

Documents:

3D Model (PDF)

Drawing (PDF)

3D Model

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19069
Crimp Quality Equipment	Yes
Overview	Solderless Terminals
Product Name	Krimptite
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	800755067545
Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.996/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	3/8" (M9)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	10, 12
Wire Size mm²	4.00-6.00
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	C-140-38
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	190690192-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19069 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 02/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION