

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193230012

Status:

Active

Overview:

Metric Ring Terminals

Description:

VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated, Bag

Documents:	
3D Model (PDF)	3D Model
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19323
Crimp Quality Equipment	Yes
Overview	Metric Ring Terminals
Product Name	VersaKrimp
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	887191289960
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	1.301/g
Packaging Type	Bag
Stud Size	M4
Wire Size AWG	N/A
Wire Size mm²	2.50-6.00
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	C6-336-M4
Reference - Drawing Numbers	
Sales Drawing	SD-19323-001-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series	
19323 Series	
Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION