

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191930120](#)  
**Status:** **Active**  
**Overview:**  
**Description:** VersaKrimp Ring Tongue Terminal for 10-12 AWG Wire

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19193](#)  
 Comments Type I Non-insulated  
 Crimp Quality Equipment Yes  
 Overview versakrimp\_terminals\_and\_splices  
 Product Name VersaKrimp  
 Taxonomy Ring and Spade Terminals  
 Type Ring  
 UPC 800755049657

**Physical**

Barrel Type Closed - Brazed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 1.814/g  
 Packaging Type Bag  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Stud Size 5/16" (M8)  
 Termination Interface: Style Crimp or Compression  
 Wire Size AWG 10, 12

**Material Info**

Engineering Number C-330-56

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing 1306-03, SD-19193-024-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19193 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description  | Product #                 |
|--|---------------------------|
| PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup> | <a href="#">640030100</a> |
| Crimp Head for the AT-200 Pneumatic Hand Tool  | <a href="#">640070100</a> |
| ServiceGrade Hand Crimp Tool - Ratchet   | <a href="#">640160038</a> |

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**