

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191930072

Status:

Active

Overview:

VersaKrimp Terminals and Splices

Description:

VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19193
Crimp Quality Equipment	Yes
Overview	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Taxonomy	Ring and Spade Terminals
Type	Ring
UPC	800755049176
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.934/g
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Size AWG	14, 16
Wire Size mm²	1.30-2.00
Material Info	
Engineering Number	BB-325-14
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	191930055-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

Green Image

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19193 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	640030100
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 02/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION