

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190030059

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²), Box, Tab 4.75 x 0.81mm

Documents:

Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-19902-008-001 (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E79133

General

Product Family

Series

Comments

Crimp Quality Equipment

Insulated

Overview

Product Name

Taxonomy

Type

UPC

Quick Disconnects

19003

Funnel Entry

Yes

Fully

Standard Quick-Disconnect Terminals

InsulKrimp

Quick Disconnects

Quick Disconnect

800753029408

Physical

Barrel Type

Color - Resin

Flammability

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Orientation

Packaging Type

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Tab Thickness

Tab Width

Temperature Range - Operating

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Closed

Blue

94V-2

Female

No

Nylon (PA)

None

Brass

Tin

Tin

Nylon

0.860/g

Straight

Bag

4.064µm

4.064µm

No

0.81mm

4.75mm

-65° to +105°C

Crimp or Compression

6.60mm max.

14, 16

1.30-2.00

Electrical

Voltage - Maximum

600V

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19003 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640010400
Hand Crimp Tool for InsulKrimp Quick Disconnect Terminals, 10-22 AWG	
Crimp Head for the AT-200 Pneumatic Hand Tool	640050400

Lead-free	Process Capability	N/A
Material Info		
Engineering Number		BB-2208X
Reference - Drawing Numbers		
Product Specification		PS-19902-008-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing		SD-19003-006-001

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION