

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193240008

Status:

Active

Overview:

Metric Ring Terminals

Description:

Avikrimp Metric Ring Terminal for Stud Size 8 (M4), Insulated Barrel

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Crimp Quality Equipment

Overview

Product Name

Taxonomy

Type

UPC

Ring and Spade Terminals

19324

Yes

Metric Ring Terminals

Avikrimp

Ring and Spade Terminals

Ring

887191290089

Physical

Barrel Type

Flammability

Insulation

Material - Metal

Material - Plating Mating

Net Weight

Packaging Type

Stud Size

Wire Size AWG

Closed - Brazed

94V-2

Nylon (PA)

Copper Alloy

Tin

1.038/g

Bag

M4

N/A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

BB2,5-837-M4

Reference - Drawing Numbers

Sales Drawing

SD-19324-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19324 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades) Crimp Head for the AT-200 Pneumatic Hand Tool	640010100
	640050100

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 02/01/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION