

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192120005](#)  
**Status:** **Active**  
**Overview:** [Wire Pins](#)  
**Description:** InsulKrimp Wire Pin Terminal for 16-14 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Crimp Terminals  
 Series [19212](#)  
 Application Power, Wire-to-Component  
 Comments Pin Length 9.40mm  
 Crimp Quality Equipment Yes  
 Overview [Wire Pins](#)  
 Packaging Alternative [192120006](#) (Adhesive Tape on Reel)  
 Product Name Wire Pin  
 Taxonomy Crimp Terminals  
 UPC 800753053366

**Physical**

Flammability 94V-0  
 Gender Male  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Net Weight 0.780/g  
 Packaging Type Bag  
 Plating min - Mating 1.016µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 4.45mm max.  
 Wire Size AWG 14, 16  
 Wire Size mm<sup>2</sup> N/A

**Material Info**

Engineering Number WP-2614X

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19212-001-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19212 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm <sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<a href="#">640010100</a>
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 10-22	<a href="#">640010300</a>

AWG (Rings,  
Spades, Hooks,  
Block Spades and  
Flanged Spades)  
Crimp Head for the 640050100  
AT-200 Pneumatic  
Hand Tool  
Crimp Head for the 640050300  
AT-200 Pneumatic  
Hand Tool  
ServiceGrade Hand 640160036  
Crimp Tool for Field  
Repair only, for  
production use our  
PremiumGrade Tool

This document was generated on 02/01/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**