

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191310018**  
**Status:** **Active**  
**Overview:** Solderless Terminals  
**Description:** InsulKrimp Block Spade Tongue Terminal for 14 to 16 AWG Wire, Stud Size 8 (M4), Length 19.80mm

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-009-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19131](#)  
 Crimp Quality Equipment Yes  
 Overview [Solderless Terminals](#)  
 Product Name InsulKrimp  
 Taxonomy Ring and Spade Terminals  
 Type Spade Block  
 UPC 800753101418

**Physical**

Barrel Type Closed  
 Color - Resin Natural  
 Flammability 94V-0  
 Insulation PVC  
 Material - Plating Mating Tin  
 Net Weight 0.737/g  
 Packaging Type Bag  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Stud Size 8 (M4)  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 4.40mm max.  
 Wire Size AWG 14, 16  
 Wire Size mm<sup>2</sup> 1.30-2.00

**Material Info**

Engineering Number BB-2781-08X

**Reference - Drawing Numbers**

Product Specification PS-19902-009-001, PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19200-1001-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19131 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

PremiumGrade [640010100](#)

Hand Crimp Tool for Avikrimp and InsulKrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm<sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)

PremiumGrade [640010300](#)

Hand Crimp Tool for InsulKrimp Terminals and Splices, 10-22

AWG (Rings,  
Spades, Hooks,  
Block Spades and  
Flanged Spades)  
Crimp Head for the 640050100  
AT-200 Pneumatic  
Hand Tool  
Crimp Head for the 640050300  
AT-200 Pneumatic  
Hand Tool  
ServiceGrade Hand 640160036  
Crimp Tool for Field  
Repair only, for  
production use our  
PremiumGrade Tool

This document was generated on 10/18/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**