

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190160075

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Krimptite Quick Disconnect, Female, for 24-26 (0.20-0.12mm²) Wire, Box, Tab 2.79 x 0.51mm

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Insulated

Overview

Product Name

Taxonomy

Type

UPC

Quick Disconnects

19016

Butted Seam

Yes

No

Standard Quick-Disconnect Terminals

Krimptite

Quick Disconnects

Quick Disconnect

800753034884

Physical

Barrel Type

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Orientation

Packaging Type

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Tab Thickness

Tab Width

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Closed

Female

No

None

None

Brass

Tin

Tin

0.226/g

Straight

Bag

2.540µm

2.540µm

No

0.51mm

2.79mm

Per Wire Specification

Crimp or Compression

24, 26

Electrical

Voltage - Maximum

Per Wire Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

M-1130

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

5304-17, SD-19016-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19016 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640030400
Crimp Head for the AT-200 Pneumatic Hand Tool	640070400

This document was generated on 02/07/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION