

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0190740025](#)  
**Status:** **Active**  
**Overview:** [Solderless Terminals](#)  
**Description:** Krimptite Steel Star Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 10 (M5)

**Documents:**

[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19074](#)  
 Crimp Quality Equipment Yes  
 Overview [Solderless Terminals](#)  
 Product Name Krimptite  
 Taxonomy Ring and Spade Terminals  
 Type Ring  
 UPC 800755072815

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 0.460/g  
 Packaging Type Bag  
 Stud Size 10 (M5)  
 Wire Size AWG 14, 16

**Material Info**

Engineering Number SRB-S-129-10

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19074 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">640031200</a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#">640071200</a>