

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191600039](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Twist Lock Splice for 14-22 AWG Wire, Grey

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-19902-013-001 \(PDF\)](#)

**Agency Certification**

CSA LR700095  
 UL E32244

**General**

Product Family Splices  
 Series [19160](#)  
 Crimp Quality Equipment Yes  
 Overview [Splices](#)  
 Product Name Closed-End Twist Lock  
 Taxonomy Splices  
 UPC 800753110434

**Physical**

Barrel Type Closed  
 Color - Resin Grey  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.431/g  
 Packaging Type Bag  
 Temperature Range - Operating 105°C  
 Wire Insulation Diameter 6.60mm max.  
 Wire Size AWG 14, 16, 18, 20, 22

**Electrical**

Voltage - Maximum 300V

**Material Info**

Engineering Number TL-G

**Reference - Drawing Numbers**

Product Specification PS-19902-013-001  
 Sales Drawing SD-19160-005-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19160 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**