

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0701070022](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 23 Circuits, Black

Documents:
[3D Model](#) [Product Specification PS-70400-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-70107-100-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [70107](#)
Application Signal, Wire-to-Wire
Comments Version A without Mounting Ears
Overview [SL Modular Connectors](#)
Product Name SL
Taxonomy Connector Housings
UPC 800755029109

Physical
Circuits (maximum) 23
Color - Resin Black
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 3.885/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers
Packaging Specification PK-70107-100-001
Product Specification PS-70400-001
Sales Drawing SD-70107-0001-0024-001



EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[70107 Series](#)

Mates With
SL Crimp Housing Versions A, G and D Only
[70066](#) (Version C and H will not mate to
the 70107 housing series) . SL Insulation
Displacement Connector Assembly,
Version G Housing [70400](#) . SL Single Row
Receptacle, Version G [70430](#)

Use With
[70021](#) SL Crimp Terminal