
This document was generated on 02/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0399800407
Status: Active
Overview: Eurostyle Terminal Blocks
Description: 5.08mm Pitch Beau Eurostyle Surface Mount Compatible Locking Header, 7 Circuits



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
3D Model (PDF)
Product Specification PS-39980-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E48521

General

Product Family	Terminal Blocks
Series	39980
Application	N/A
Comments	Gold plating available
Component Type	PCB Header
Overview	Eurostyle Terminal Blocks
Product Name	Eurostyle Pluggable
Taxonomy	Terminal Blocks and Barrier St
Type	Euro Block
UPC	800753317277

Physical

Circuits (Loaded)	7
Color - Resin	Black
Entry Angle	N/A
Flammability	94V-0
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.060/lb
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.81mm
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Panel Mount	No
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	Yes
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	140°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

Material Info

Engineering Number	981507

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
39980 Series

Mates With
399802107 Spring Clamp Plug, 399800307 Screw Clamp Plug

Reference - Drawing Numbers

Product Specification	PS-39980-001-001
Sales Drawing	SD-39980-006-001

This document was generated on 02/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION