

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0701070014](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 15 Circuits, Black

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-70400-001 \(PDF\)](#)
[3D Model](#) [Packaging Specification PK-70107-100-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [70107](#)
Application Signal, Wire-to-Wire
Comments Version A without Mounting Ears
Overview [SL Modular Connectors](#)
Product Name SL
Taxonomy Connector Housings
UPC 800754346498

Physical
Circuits (maximum) 15
Color - Resin Black
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 2.605/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers
Packaging Specification PK-70107-100-001
Product Specification PS-70400-001
Sales Drawing SD-70107-0001-0024-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[70107 Series](#)

Mates With
SL Crimp Housing Versions A, G and D Only [70066](#) (Version C and H will not mate to the 70107 housing series) . SL Insulation Displacement Connector Assembly, Version G Housing [70400](#) . SL Single Row Receptacle, Version G [70430](#)

Use With
[70021](#) SL Crimp Terminal