

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2070170014](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Sigma Sealed Plug Housing, Dual Row, 4.20mm Pitch, 14 Circuits, UL94V-0, Natural

Documents:	
3D Model	Packaging Specification 2070170000-PK-000 (PDF)
Drawing (PDF)	Test Summary 2070170000-TS-000 (PDF)
3D Model (PDF)	Test Summary 2070170001-TS-000 (PDF)
Product Specification 2070170000-PS-000 (PDF)	Datasheet (PDF)
Application Specification 2070170000-AS-000 (PDF)	RoHS Certificate of Compliance (PDF)


Agency Certification	
UL	E29179

General	
Product Family	Crimp Housings
Series	207017
Application	Power, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma
Taxonomy	Connector Housings
UPC	193264428540

Physical	
Circuits (maximum)	14
Color - Resin	Natural
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	7.600/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers	
Application Specification	2070170000-AS-000
Packaging Specification	2070170000-PK-000
Product Specification	2070170000-PS-000
Sales Drawing	2070170000-SD-000
Test Summary	2070170000-TS-000, 2070170001-TS-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2022)4187-DC (10 June 2022) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[207017](#) Series

Mates With
Mini-Fit Jr. Receptacle Housing [5557](#) ,
[46992](#) . Mini-Fit TPA2 Receptacle Housing
[172708](#)

Use With
Mini-Fit Sigma Sealed Cap [2070190014](#) .
Mini-Fit Sigma TPA Retainer [1727092007](#) .
Mini-Fit TPA2/Sigma Male Crimp Terminal
[172765](#) , [203070](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION