

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0347290161

Status:

Active

Overview:

Description:

Stac64 Receptacle Housing, 16 Circuits, Dual Row, Polarization B, Gray, Tray

General	
Product Family	Crimp Housings
Series	34729
Application	Automotive, Signal, Wire-to-Board
Overview	stac64_single_multipocket_and_hybrid_header_system
Polarization	B
Product Name	Stac64
Taxonomy	Connector Housings
UPC	884982006591
Physical	
Circuits (maximum)	16
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	6.420/g
Number of Rows	2
Packaging Type	Tray
Panel Mount	N/A
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	10.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	347290200-AS-CH-000, AS-34729-020-001
Packaging Specification	PK-31301-201-001
Product Specification	PS-34729-020-001
Sales Drawing	SD-34729-020-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34729 Series

Mates With

34690 2.54mm Pitch Stac64 Vertical Header, 34691 2.54mm Pitch Stac64 Right Angle Header

Use With

34803 CTX64 Female Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION