

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009483025

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 396 PC Board Connector, Right Angle, Polyester Connector, Gold (Au) Selective, 2 Circuits

Documents:

- 3D Model

Packaging Specification PK-41815-001-000 (PDF)
- Drawing (PDF)

Symbol Footprint Data SYM-09-48-1024-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50-001 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Receptacles

Series

41815

Application

Board-to-Board, Power

Component Type

PCB Receptacle

Overview

KK Interconnect Systems

Product Name

KK 396

Taxonomy

PCB Headers and Receptacles

UPC

800754221115

Physical

Circuits (Loaded)

2

Circuits (maximum)

2

Color - Resin

Natural

Flammability

94V-0

Glow-Wire Capable

No

Lock to Mating Part

Yes

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

Polyester

Net Weight

0.705/g

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.68mm

PCB Locator

No

PCB Retention

Yes

Packaging Type

Tray

Pitch - Mating Interface

3.96mm

Plating min - Mating

0.381µm

Plating min - Termination

2.540µm

Polarized to PCB

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

5.0A

Voltage - Maximum

250V

Solder Process Data

Duration at Max. Process Temperature (seconds)

005

Lead-freeProcess Capability

WAVE

Max. Cycles at Max. Process Temperature

001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

41815 Series

Mates With

KK 396 Header [41771](#) , [41772](#) , [41791](#) ,
[41792](#) , [42491](#) , [42492](#) , [42891](#) , [41661](#) ,
[41662](#) , [41671](#) , [41672](#) , [41681](#)

Process Temperature max. C	235
Material Info	
Engineering Number	A-41815-0425
Reference - Drawing Numbers	
Packaging Specification	PK-41815-001-000
Product Specification	PS-08-50-001
Sales Drawing	SDA-41815-000
Symbol/Footprint Data	SYM-09-48-1024-001

This document was generated on 01/04/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION