

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936000337

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect Plastic Gable Gland, with Gasket, M12x1.5 Thread, Grey RAL 7001



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP68 with Gasket
IP Rating	IP68
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
Standard	DIN EN 50262, EN 60529
Taxonomy	Heavy-Duty Cable Glands
UPC	887191850894
Physical	
Cable Diameter	3.00-6.50mm
Flammability	UL 94V-2
Gland Color	Grey RAL 7001
Material - Cable Gland	Polyamide
Material - Gasket	NBR
Material - Nut	Polyamide
Net Weight	4.667/g
Packaging Type	Bag
Panel Cutout Diameter	12.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +100°C
Thread Size	M12x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68
Material Info	
Engineering Number	7000.7821.0

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of	CER_4000432592_00_000.pdf
Conformity	
ZZCERT_UKCA - Declaration of	CER_4000402294_00_000.pdf
Conformity	

Search Parts in this Series

93600 Series

Use With

Sealed Enclosures and Boxes

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION