

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731120217](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Machined Contact, Female, Crimp, 0.20µm Gold Plating, Split Tine, 18-22 AWG

Documents:

[Drawing \(PDF\)](#) [Brochure \(PDF\)](#)
[Packaging Specification 1731120004-PK-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	D-Sub Products
Series	173112
Contact Type	Machined Crimp
Overview	FCT D-Sub Connectors
Product Category	Contacts
Product Name	FCT Products
Taxonomy	D-Sub Contacts
Type	Standard Density
UPC	889056489720

Physical

Durability (mating cycles max)	200
Gender	Female
Material - Contact	Brass
Net Weight	0.200/g
Orientation	Straight
Packaging Type	Bag
Plating - Contact	Gold over Nickel
Plating min - Mating	0.200µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +130°C
Termination Style	Crimp
Wire Size AWG	18, 20, 22

Electrical

Current - Maximum per Contact	7.5A
-------------------------------	------

Material Info

Engineering Number	FK20SL18-02V-5783
--------------------	-------------------

Reference - Drawing Numbers

Packaging Specification	1731120004-PK-000
Sales Drawing	1731120203-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[173112 Series](#)

Use With

FCT Standard-Density Connectors