

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026034201

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, Friction Ramp, 20 Circuits, Natural

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-40-02-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

6442

Power, Wire-to-Board

KK Interconnect Systems

KK 396

Connector Housings

800753626966

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

20

Natural

94V-2

Receptacle

No

Yes

Nylon

5.272/g

1

Bag

No

3.96mm

No

See Product Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

6442-R20-Z

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-40-02-001

SD-6442-001, SD-6442-002, SD-6442-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

6442 Series

Mates With

Molex 3.96mm pitch KK headers

Use With

MarKK Crimp Terminals 45570
KK Trifurcon Crimp Terminals 6838 , 7258
L1NK 396 Pre-Crimped Lead 797582145 , 797582146

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION