

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0534261510

Status:

Active

Overview:

Mini-Lock Wire-to-Board Connector System

Description:

2.50mm Pitch, Mini-Lock PCB Header, Single Row, Right-Angle, Through Hole with Kinked Pins, Tin Plating, Positive Lock, 15 Circuits, Tray, 3.40mm PC Tail Length

Documents:

3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification 511630000-PS-000 (PDF)

Product Specification 511631000-PS-000 (PDF)

Product Specification PS-51103-005-001 (PDF)

Packaging Specification SPK-53426-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Component Type

Overview

Product Name

Taxonomy

UPC

PCB Headers

53426

Signal, Wire-to-Board

PCB Header

Mini-Lock Wire-to-Board Connector System

Mini-Lock

PCB Headers and Receptacles

800754357227

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

15

15

Natural

30

94V-0

No

None

Yes

Phosphor Bronze

Tin

Tin

Polyester

1854.900/mg

1

Right Angle

3.40mm

No

Yes

1.60mm

Tray

2.50mm

Yes

No

Fully

No

-55° to +105°C

Through Hole - Kinked Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2022)4187-DC (10

June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

53426 Series

Mates With

Mini-Lock Receptacle 51163 . Mini-Lock Cable Assembly 15137

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-53426-002-001
Product Specification	511630000-PS-000, 511631000-PS-000, PS-51103-005-001
Sales Drawing	534260000-SD-000

This document was generated on 01/03/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION