

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0530481310

Status:


Active

Overview:

PicoBlade Connector System

Description:

1.25mm Pitch, PicoBlade PCB Header, Single Row, Right-Angle, Through Hole, Tin (Sn) Plating, Friction Lock, 13 Circuits, Tray, 2.30mm PC Tail Length



Documents:	
3D Model	Product Specification 510211111-PS-000 (PDF)
Drawing (PDF)	Application Specification 510210000-AS-000 (PDF)
2D Drawing (DXF)	Packaging Specification SPK-53048-001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
2D Drawing DXF (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 510211010-PS-000 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	53048
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	PicoBlade Connector System
Product Name	PicoBlade
Taxonomy	PCB Headers and Receptacles
UPC	800753565975
Physical	
Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	3.50mm
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	294.200/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Through Hole

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

53048 Series

Mates With

PicoBlade Housing 51021

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Application Specification	510210000-AS-000
Packaging Specification	SPK-53048-001-001
Product Specification	510211010-PS-000, 510211111-PS-000
Sales Drawing	530480001-SD-000

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION