

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0026033161](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, 16 Circuits, Natural

Documents:

3D Model	Product Specification PS-40-02-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
3D Model (PDF)	

Agency Certification

CSA	LR19980
-----	---------

General

Product Family	Crimp Housings
Series	6442
Application	Power, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
Taxonomy	Connector Housings
UPC	800753587342

Physical

Circuits (maximum)	16
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	4.160/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Stackable	No
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	6442-16-Z
--------------------	-----------

Reference - Drawing Numbers

Product Specification	PS-40-02-001
Sales Drawing	SD-6442-001, SD-6442-002, SD-6442-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[6442](#) Series

Mates With

Molex 3.96mm pitch KK headers

Use With

MarKK Crimp Terminals [45570](#)
KK Trifurcon Crimp Terminals [6838](#) , [7258](#)
L1NK 396 Pre-Crimped Lead [797582145](#) , [797582146](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION