

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015311063

Status:

Active

Description:

4.80mm Pitch Wire-to-Wire Plug Housing, 6 Circuits, Natural

Documents:	
3D Model	Product Specification PS-5025-002-001 (PDF)
3D Model (PDF)	Product Specification PS-5025-003-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-5025-001-001 (PDF)
Product Specification PS-5025-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5025
Application	Power, Wire-to-Wire
Product Name	N/A
Taxonomy	Connector Housings
UPC	800753622005
Physical	
Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	2160.800/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Engineering Number	5025-06P1
Reference - Drawing Numbers	
Packaging Specification	SPK-5025-001-001
Product Specification	PS-5025-001-001, PS-5025-002-001, PS-5025-003-001
Sales Drawing	SD-5025-06PX-001, SD-5025-06PX-002

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5025 Series

Mates With

15311062 Receptacle

Use With

5006

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION