

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026034141

Status:

Active

Overview:

KK Interconnect Systems

Description:

KK 3.96mm Crimp Terminal Housing, Use With Trifurcon Terminals, Friction Ramp, 14 Circuits, Natural

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-40-02-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

6442

Power, Wire-to-Board

KK Interconnect Systems

KK 396

Connector Housings

800753626942

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

14

Natural

94V-2

Receptacle

No

Yes

Nylon

3.712/g

1

Bag

No

3.96mm

No

See Product Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

6442-R14-Z

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-40-02-001

SD-6442-001, SD-6442-002, SD-6442-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

6442 Series

Mates With

Molex 3.96mm pitch KK headers

Use With

MarKK Crimp Terminals [45570](#)
KK Trifurcon Crimp Terminals [6838](#) , [7258](#)
L1NK 396 Pre-Crimped Lead [797582145](#) , [797582146](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION