

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015311043

Status:

Active

Description:

4.80mm Pitch Wire-to-Wire Plug Housing, 4 Circuits

Documents:	
3D Model	Product Specification PS-5025-002-001 (PDF)
Drawing (PDF)	Product Specification PS-5025-003-001 (PDF)
3D Model (PDF)	Packaging Specification SPK-5025-001-001 (PDF)
Product Specification PS-5025-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5025
Application	Power, Wire-to-Wire
Product Name	N/A
Taxonomy	Connector Housings
UPC	800754214032
Physical	
Circuits (maximum)	4
Flammability	94V-2
Gender	Plug
Glow-Wire Capable	No
Net Weight	1567.400/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Engineering Number	5025-04P1
Reference - Drawing Numbers	
Packaging Specification	SPK-5025-001-001
Product Specification	PS-5025-001-001, PS-5025-002-001, PS-5025-003-001
Sales Drawing	SD-5025-04PX-001, SD-5025-04PX-002

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

5025 Series

Mates With

15311042 Receptacle

Use With

5006

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION