

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2127242071](#)
Status: **Active**
Overview: [Micro-One Wire-to-Board Connector System](#)
Description: Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Glow-Wire Capable, 7 Circuits

Documents:	
3D Model	Product Specification 2059790000-PS-000 (PDF)
Drawing (PDF)	Application Specification 2059790000-AS-000 (PDF)
2D Drawing DXF (PDF)	Packaging Specification 2127249200-SPK-200 (PDF)
3D Model (PDF)	Datasheet (PDF)
2D Drawing (DXF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [212724](#)
Application Signal, Wire-to-Board
Overview [Micro-One Wire-to-Board Connector System](#)
Product Name Micro-One
Taxonomy Connector Housings
UPC 193264613878

Physical

Circuits (maximum) 7
Color - Resin Black
Gender Receptacle
Glow-Wire Capable Yes
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Polyamide
Net Weight 497.650/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.00mm
Polarized to Mating Part No
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification 2059790000-AS-000
Packaging Specification 2127249200-SPK-200
Product Specification 2059790000-PS-000
Sales Drawing 2127240000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[212724](#) Series

Mates With

Micro-One Vertical Header [205971](#) , [217063](#)
. Micro-One Right-Angle Header [205972](#) ,
[217064](#)

Use With

Micro-One TPA Retainer [212725](#) . Micro-
One Female Crimp Terminal [561349001](#)
(22-24 AWG), [561349002](#) (26-28 AWG)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION