

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2041020409

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Friction Lock, Natural, Glow-Wire Capable



Documents:	
3D Model	Application Specification 351500000ASKOR-000 (PDF)
3D Model (PDF)	Packaging Specification 2041020609-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification 2041020609-000 (PDF)	Brochure (PDF)
Application Specification 351500000ASENG-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	204102
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
Taxonomy	Connector Housings
UPC	191128287784
Physical	
Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	3.356/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm, 8.50mm
Pitch - Termination Interface	8.00mm, 8.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	2041020609-001
Product Specification	2041020609-000
Sales Drawing	2041020409-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per -	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

204102 Series

Mates With

VersaBlade Multi-Module 4-2 Receptacle Housing 2041020609

Use With

VersaBlade Crimp Terminals 35746 (ckt 1, 2), 35745 (ckt 3, 4)
 VersaBlade TPA 359650290 , 359650292 , 359650293 , 1040810282 , 495470392 (Upper), 495480390 (Lower)