

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0009508101](#)  
**Status:** **Active**  
**Overview:** [KK Interconnect Systems](#)  
**Description:** KK 3.96mm Crimp Terminal Housing, Friction Ramp, 10 Circuits, Natural

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-08-50-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Drawing (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">41695</a>
Application	Power, Wire-to-Board
Overview	<a href="#">KK Interconnect Systems</a>
Product Name	KK 396
Taxonomy	Connector Housings
UPC	800754227902

**Physical**

Breakaway	No
Circuits (maximum)	10
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	3.332/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

**Solder Process Data**


Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	41695-N-B10
--------------------	-------------

**Reference - Drawing Numbers**

Product Specification	PS-08-50-001
Sales Drawing	SD-41695-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[41695 Series](#)

**Mates With**

KK 396 Header [41791](#) , [41792](#) , [41671](#) ,  
[41672](#) , [41661](#) , [41662](#)

**Use With**

KK 396 Crimp Terminals [2478](#) , [2578](#) , [6838](#)  
, [7258](#) , [45570](#) <br>L1NK 396 Pre-Crimped  
Lead [797582145](#) , [797582146](#)