

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1502010014](#)
Status: **Active**
Overview: [Ditto Wire-to-Wire Interconnects](#)
Description: Ditto Hermaphroditic Crimp Housing, Positive Lock, 4 Circuit, High-Temperature, Natural

Documents:

3D Model	Product Specification 1502000000-TS-000 (PDF)
Drawing (PDF)	Application Specification 1502000000-AS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-150170-0000-000 (PDF)
Product Specification 1502000000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	150201
Application	Power, Wire-to-Wire
Overview	Ditto Wire-to-Wire Interconnects
Product Name	Ditto
Taxonomy	Connector Housings
UPC	191130051687

Physical

Circuits (maximum)	4
Color - Resin	Natural (White)
Gender	Hermaphroditic
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.791/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +150°C

Material Info

Reference - Drawing Numbers

Application Specification	1502000000-AS-000
Packaging Specification	PK-150170-0000-000
Product Specification	1502000000-PS-000, 1502000000-TS-000
Sales Drawing	1502010000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[150201](#) Series

Mates With

Identical Housing [1502010014](#)

Use With

Ditto High-Temperature Hermaphroditic
Terminals [1502000011](#) , [1502000012](#) ,
Ditto High-Temperature TPA Retainer
[1502120014](#)