

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2074580005](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: KK Plus 396 Receptacle Housing, 3.96mm Pitch, Single Row, 5 Circuits, UL 94V-0, Black

Documents:

3D Model	Product Specification 2074580000-PS-JP-000 (PDF)
3D Model (PDF)	Product Specification 2074580000-PS-SK-000 (PDF)
Drawing (PDF)	Product Specification 2074580000-TS-000 (PDF)
Product Specification 2074580000-PS-000 (PDF)	Packaging Specification 2074580000-PK-000 (PDF)
Product Specification 2074580000-PS-CH-000 (PDF)	Datasheet (PDF)
Product Specification 2074580000-PS-ES-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	Crimp Housings
Series	207458
Application	Power, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK Plus
Taxonomy	Connector Housings
UPC	191130115594

Physical

Circuits (maximum)	5
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.790/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2074580000-PK-000
Product Specification	2074580000-PS-000, 2074580000-PS-CH-000, 2074580000-PS-ES-000, 2074580000-PS-JP-000, 2074580000-PS-SK-000, 2074580000-TS-000
Sales Drawing	2074580000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[207458](#) Series

Mates With

KK Plus 396 Headers [207478](#) , [207479](#)

Use With

Female Crimp Terminal [455703000](#) ,
[455703002](#) , [455703050](#) , [455703052](#) . KK
Plus 396 TPA Retainer [207459](#)