

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0351510319

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural, Glow-Wire Capable

- Documents:
- 3D Model (PDF)

Application Specification 351500000ASKOR-000 (PDF)
- 3D Model

Packaging Specification PK-35151-004-001 (PDF)
- Drawing (PDF)

Datasheet (PDF)
- Product Specification PS-35150-001-001 (PDF)

Brochure (PDF)
- Product Specification PS-35150-003-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 351500000ASENG-000 (PDF)

|                      |                                          |
|----------------------|------------------------------------------|
| Agency Certification |                                          |
| CSA                  | LR19980                                  |
| UL                   | E29179                                   |
| General              |                                          |
| Product Family       | Crimp Housings                           |
| Series               | 35151                                    |
| Application          | Power, Wire-to-Wire                      |
| Overview             | VersaBlade Wire-to-Wire Connector System |
| Product Name         | VersaBlade                               |
| Taxonomy             | Connector Housings                       |
| UPC                  | 756054256985                             |

|                               |                |
|-------------------------------|----------------|
| Physical                      |                |
| Breakaway                     | No             |
| Circuits (maximum)            | 3              |
| Color - Resin                 | Natural        |
| Flammability                  | 94V-0          |
| Gender                        | Plug           |
| Glow-Wire Capable             | Yes            |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | PET/PC         |
| Net Weight                    | 2.740/g        |
| Number of Rows                | 1              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 7.30mm         |
| Pitch - Termination Interface | 7.30mm         |
| Polarized to Mating Part      | Yes            |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +110°C |

Material Info

|                             |                                          |
|-----------------------------|------------------------------------------|
| Reference - Drawing Numbers |                                          |
| Application Specification   | 351500000AS_ENG-000, 351500000AS_KOR-000 |
| Packaging Specification     | PK-35151-004-001                         |
| Product Specification       | PS-35150-001-001, PS-35150-003-001       |
| Sales Drawing               | SD-35151-031-001, SD-35151-031X-001      |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

35151 Series

Mates With

VersaBlade Receptacle Housing 35150  
<br>VersaBlade Multi-Module 2-3-4  
Receptacle Housing 35524 , 2026500909

Use With

VersaBlade Crimp Terminals 35746 (ckt 1), 35745 (ckt 2), 35748 (ckt 3) <br>VersaBlade TPA 351500390 , 351500392 , 351500393 , 351500394

This document was generated on 10/19/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**