

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5024391400

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

CLIK-Mate Plug Housing, 2.00mm Pitch, Single Row, Positive Lock, 14 Circuits, White

Documents:	
Drawing (PDF)	Application Specification AS-502439-001-001 (PDF)
3D Model	Application Specification AS-502439-002-001 (PDF)
3D Model (PDF)	Packaging Specification 5024399200-200 (PDF)
Product Specification 5024431570-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	502439
Application	Signal, Wire-to-Board
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
Taxonomy	Connector Housings
UPC	822350915922
Physical	
Breakaway	No
Circuits (maximum)	14
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	907.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	3.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-502439-001-001, AS-502439-002-001
Packaging Specification	5024399200-200
Product Specification	5024431570-000
Sales Drawing	5024391500-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

502439 Series

Mates With

502443 PCB Receptacle Vertical . 502494 PCB Receptacle Right Angle

Use With

CLIK-Mate Terminal 502438 . CLIK-Mate Pre-Crimped Leads 797581014 , 797581015