

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5046940200

Status:

Active

Overview:

Description:

CP-3.3 Plug Housing, 3.30mm Pitch, Single Row, Polarized, Positive Inertia Lock, 2 Circuits, Natural

Agency Certification	
UL	E29179
General	
Product Family	Crimp Housings
Series	504694
Application	Signal, Wire-to-Wire
Overview	cp65_wiretoboard_connector_system
Product Name	CP-3.3
Taxonomy	Connector Housings
UPC	887191361369
Physical	
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1132.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.30mm
Pitch - Termination Interface	3.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-504693-001-001, AS-504693-002-001
Packaging Specification	SPK-504694-001-001
Product Specification	PS-504693-001-001
Sales Drawing	5046940000-SD-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

504694 Series

Mates With

Receptacle Housing [5046930200](#)

Use With

Terminal Retainer [504695](#) . Plug Crimp Terminal [50398](#) , [505608](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION