

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009508020](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: [KK 3.96mm Crimp Terminal Housing, 2 Circuits, Natural](#)

Documents:

3D Model (PDF)	Product Specification PS-08-50-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	41695
Application	Power, Wire-to-Board
Overview	KK Interconnect Systems
Product Name	KK 396
Taxonomy	Connector Housings
UPC	800754227568

Physical

Breakaway	No
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	0.667/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	41695-N-A02
--------------------	-------------

Reference - Drawing Numbers

Product Specification	PS-08-50-001
Sales Drawing	SD-41695-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[41695 Series](#)

Mates With

KK 396 Header [41791](#) , [41792](#) , [41671](#) ,
[41672](#) , [41661](#) , [41662](#)

Use With

KK 396 Crimp Terminals [2478](#) , [2578](#) , [6838](#)
, [7258](#) , [45570](#)
L1NK 396 Pre-Crimped
Lead [797582145](#) , [797582146](#)