

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5024390200

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

CLIK-Mate Plug Housing, 2.00mm Pitch, Single Row, Positive Lock, 2 Circuits, White



Documents:	
3D Model (PDF)	Application Specification AS-502439-001-001 (PDF)
3D Model	Application Specification AS-502439-002-001 (PDF)
Drawing (PDF)	Packaging Specification 5024399200-200 (PDF)
Product Specification 5024431570-000 (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Crimp Housings
Series	502439
Application	Signal, Wire-to-Board
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate
Taxonomy	Connector Housings
UPC	822350915700
Physical	
Breakaway	No
Circuits (maximum)	2
Color - Resin	White
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	279.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	3.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-502439-001-001, AS-502439-002-001
Packaging Specification	5024399200-200
Product Specification	5024431570-000
Sales Drawing	5024391500-000

EU ELV
Not Relevant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
502439 Series

Mates With
502443 PCB Receptacle Vertical . 502494
PCB Receptacle Right Angle

Use With
CLIK-Mate Terminal 502438 . CLIK-Mate
Pre-Crimped Leads 797581014 , 797581015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION