

EV Charging Cable



Type Approved
Safety
Regular Production
Surveillance
www.tuv.com
ID 1111246575

Product Variants

Power	Art.-No.	Length	Weight	Voltage	Current	Phase
7 kW	E100001	5m	1,98kg	230V	32A	Single
	E100004	7m	2,53kg	230V	32A	Single
11 kW	E100002	5m	2,16kg	380V	16A	Three
	E100005	7m	2,79kg	380V	16A	Three
22 kW	E100003	5m	3,12kg	380V	32A	Three
	E100006	7m	4,06kg	380V	32A	Three

Product Parameters

Rated Current	16A / 32A	Cable Jacket	TPU
Water Protection	IP55	Cable Length	5m / 7m
Working Temperature	-30°C ~ +50°C	Standard	IEC 62796-1, IEC62796-2
Charging Mode	3	Flammability class	UL94-V0
Plug Connector	Type 2 / Type 2	Mating cycles	10.000
Scope of delivery	Charging cable, stable carrier bag	Save to drive over	Up to 1.8t

Logistic Data

Article	Art.-No.	EAN	Packaging Dimensions	Gross Weight
7kW – 5m	E100001	6974257510183	360 x 400 x 120 mm	2,96kg
7kW – 7m	E100004	6974257510190	360 x 400 x 160 mm	3,67kg
11kW – 5m	E100002	6974257510169	360 x 400 x 120 mm	3,14kg
11kW – 7m	E100005	6974257510176	360 x 400 x 160 mm	3,93kg
22kW – 5m	E100003	6974257510145	360 x 400 x 120 mm	4,10kg
22kW – 7m	E100006	6974257510152	360 x 400 x 160 mm	5,20kg