
# **TRACO POWER**


### **Common Mode Choke**

Order Code	ТСК-090
Inductance (each winding)	<b>470 μH ±25%</b> (at 10 kHz / 100 mV)
Impedance (DCR)	60 mΩ max.
Rated Current	1 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions

#### Impedance Curve



#### **Outline Dimensions**



<sup>3</sup> 3.05 4PL

2 m TOP VIEW

Dimensions [mm]	
Α	9.2 max.
В	11.8 max.
С	5.0 max.
Marking	470UH

All specifications valid at +25°C, unless otherwise stated.

© Copyright 2023 Traco Electronic AG

**TRACO POWER** 

www.tracopower.com

Specifications can be changed without notice. Rev. September 19, 2023 Page 1 / 1

## TCK-090