## **II TRACO POWER**


## **Common Mode Choke**

**TCK-119** 


Order Code	TCK-119
Inductance (each winding)	<b>419 μH ±25%</b> (at 10 kHz / 50 mV)
Impedance (DCR)	117 mΩ max.
Rated Current	0.78 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions



## Impedance Curve




## **Outline Dimensions**



<b>Dimensions</b> [mm]	
Α	7.5 max.
В	8.5 max.
С	10.5 max.
D	3.5 ±1.0
E	5.08 ±0.5
F	2.54 ±0.3
G	ø 0.6 ±0.1

All specifications valid at +25°C, unless otherwise stated.



Specifications can be changed without notice.