

VOLTCRAFT

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

CE

ENDOSCOPE CAMERA VGA FLEXCAM SF/LF

Item no: 2793312-17

This product serves as a camera attachment for endoscopes BS-1000T for visual fault tracing or inspection with dead-voltage systems and equipment.



FEATURES

Flexible neck positions, camera // LED's for shooting in darkness // Water resistant camera and neck

TECHNICAL DATA

Item No.:	Length (m)	Depth of field (cm)	Insertion tube
2793312	2	1.5 - 6	Flexible
2793313	5	4 - ∞	Flexible
2793314	10	4 - ∞	Flexible in spool
2793315	1	1.5 - 6	Semi-rigid
2793316	1	4 - ∞	Semi-rigid
2793317	2	1.5 - 6	Semi-rigid

Suitable for	BS-1000T
Diameter Ø	5.5 mm
Field of view	65°
Resolution (dynamic, static)	640 x 480 px
White balance	automatic
Camera lighting	20 LEDs; 1200 ±10 % Lux at 20 mm
Bend radius	>5 cm
Operating conditions	-20 to +60 °C, max. 95 % RH (non-condensing)
Storage conditions	-20 to +60 °C, max. 95 % RH (non-condensing)
Protection class	IP67 (camera, camera neck)

CONTENTS

Endoscope camera // Protective cap // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2793312-17_V2_1125_en_ds 9007200254182795 I2/Q2 en