



USB-C 3.1 MALE - FEMALE EXTENSION CABLE




These USB-C Male to USB-C Female Extension cables support Power Delivery (PD) charging at 60 watts (20v/@3A), USB 3.1 (Gen 1) 5Gb/s data transfer speeds, and can be used as a video cable 5k@60Hz video output (Thunderbolt 3) and audio transmission.

NOTE: Precise performance is dependent upon all cables and devices connected. Available in 6 lengths. Colours Black or White.

Cable OD: 4.5mm

Temperature Range: -55 to +85°C



VARIANTS

- FCR72000** - USB-C Extension cable 0.3m Black
- FCR72001** - USB-C Extension cable 0.5m Black
- FCR72001W** - USB-C Extension cable 0.5m White
- FCR72002** - USB-C Extension cable 0.75m Black
- FCR72003** - USB-C Extension cable 1m Black
- FCR72003W** - USB-C Extension cable 1m White
- FCR72004** - USB-C Extension cable 1.5m Black
- FCR72005** - USB-C Extension cable 2m Black
- FCR72005W** - USB-C Extension cable 2m White

WIRE CONNECTION

SHIELD	SHIELD	34AWG	GROUND
A10	A10		RX2-
A11	A11	34AWG	RX2+
B3	B3	34AWG	TX2-
B2	B2	34AWG	TX2+
B10	B10	34AWG	RX1-
B11	B11	34AWG	RX1+
A3	A3	34AWG	TX1-
A2	A2	34AWG	TX1+
A7	A7 B7	32AWG	D-
A6	A6 B6	32AWG	D+
B8	B8	34AWG	SBU2
A8	A8	34AWG	SBU1
B5	B5	34AWG	Vconn
A5	A5	34AWG	CC
A4.B4.A9.B9	A4.B4.A9.B9	24AWG	VBUS
A1.B1.A12.B12	A1.B1.A12.B12	24AWG	GND
TYPE-C 3.1 M	TYPE-C 3.1 M	CABLE AWG	CABLE FUNCTION