

KLL/KLÖ hook and loop cable tie



Velcro tie

Particularly suited for sensitive cables and lines that are to be bundled or fastened without kinking or pinching.

Velcro binders exert only low pressure on the lines and lie evenly and flush.

Suitable for up to 10,000 actuations in reusable bundling applications.

Material

KLL - Polyamide sleeve / PE mushroom head tape / with punched hole

Note

KLL – pre-punched on rolls

KLÖ – Packed small in poly bags

Technical data

Temperature range: -40°C up to +85°C

KLL with punched hole

Part no.	Colour	Length mm	Width mm	Bundle Ø mm	Unit	Net EUR/100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
93730	black	150,0	20,0	45,0	1000	o. r.	o. r.	o. r.
93731	black	200,0	20,0	60,0	750	o. r.	o. r.	o. r.
93732	black	330,0	20,0	100,0	450	o. r.	o. r.	o. r.

KLÖ with plastic eye

Part no.	Colour	Length mm	Width mm	Bundle Ø mm	Unit	Net EUR/100 items at a purchase of		
						up to 100	101 - 500	501 - 1000
93735	red-black	195,0	25,0	55,0	10	o. r.	o. r.	o. r.
93736	red-black	240,0	25,0	70,0	10	o. r.	o. r.	o. r.
93737	red-black	360,0	25,0	110,0	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request