


TY-RAP® cable tie with steel lug lock



TY-RAP® transparent

Cable tie with steel lug lock made of corrosion-resistant, non-magnetic steel. This technology enables the cable tie to offer excellent binding properties even under the most rigorous conditions such as heat, cold, humidity etc. and makes it insensitive to vibrations and external influences.

Material

Polyamide 6.6

- halogen-free

Note

Brown, red, orange, yellow, green, purple or grey available on request.

Technical data

Temperature range: -60°C up to +85°C

Flammability acc. to UL 94: V2

Part no. transparent	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Unit	Net EUR/100 items at a purchase of		
							up to 1000	1001 - 5000	5001 - 10000
91051	TYB 23M	92,0	2,4	16,0	80,0	1000	o. r.	o. r.	o. r.
91055	TY 232M	203,0	2,4	50,0	80,0	1000	o. r.	o. r.	o. r.
91058	TY 234M	356,0	2,4	102,0	80,0	1000	o. r.	o. r.	o. r.
91061	TYB 24M	140,0	3,6	29,0	180,0	1000	o. r.	o. r.	o. r.
91064	TY 242M	204,0	3,6	50,0	180,0	1000	o. r.	o. r.	o. r.
91067	TY 26M	284,0	3,6	76,0	130,0	1000	o. r.	o. r.	o. r.
91070	TY 244M	368,0	3,6	103,0	130,0	1000	o. r.	o. r.	o. r.
91073	TYB 25M	186,0	4,8	45,0	220,0	1000	o. r.	o. r.	o. r.
91076	TY 253M	295,0	4,8	78,0	220,0	1000	o. r.	o. r.	o. r.
91079	TY 28M	361,0	4,8	102,0	220,0	1000	o. r.	o. r.	o. r.
91082	TY 272M	223,0	6,9	50,0	540,0	500	o. r.	o. r.	o. r.
91085	TY 27M	340,0	6,9	90,0	540,0	500	o. r.	o. r.	o. r.
91088	TY 29M	771,0	6,9	229,0	540,0	500	o. r.	o. r.	o. r.

small package

Part no. transparent	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Unit	Net EUR/100 items at a purchase of		
							up to 1000	1001 - 5000	5001 - 10000
91050	TY 5-23M	92,0	2,4	16,0	80,0	100	o. r.	o. r.	o. r.
91054	TY 5-232M	203,0	2,4	50,0	80,0	100	o. r.	o. r.	o. r.
91057	TY 5-234M	356,0	2,4	102,0	80,0	100	o. r.	o. r.	o. r.
91060	TY 5-24M	140,0	3,6	29,0	180,0	100	o. r.	o. r.	o. r.
91063	TY 5-242M	204,0	3,6	50,0	180,0	100	o. r.	o. r.	o. r.
91066	TY 5-26M	284,0	3,6	76,0	130,0	100	o. r.	o. r.	o. r.
91069	TY 5-244M	368,0	3,6	103,0	130,0	100	o. r.	o. r.	o. r.
91072	TY 5-25M	186,0	4,8	45,0	220,0	100	o. r.	o. r.	o. r.
91075	TY 5-253M	295,0	4,8	78,0	220,0	100	o. r.	o. r.	o. r.
91078	TY 5-28M	361,0	4,8	102,0	220,0	100	o. r.	o. r.	o. r.
91081	TY 5-272M	223,0	6,9	50,0	540,0	50	o. r.	o. r.	o. r.
91084	TY 5-27M	340,0	6,9	90,0	540,0	50	o. r.	o. r.	o. r.
91087	TY 5-29M	771,0	6,9	229,0	540,0	50	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request