

TY-MX cable tie with steel lug lock



TY-RAP® (UV-stabilised)

Cable tie with steel lug lock made of corrosion-resistant, non-magnetic steel.

This technology enables the cable tie to offer excellent binding properties even under the most rigorous conditions such as heat, cold, humidity etc. and makes it insensitive to vibrations and external influences.

Material

Polyamide 6.6
UV-resistant

- halogen-free
- silicone-free

Note

Other colours and materials available on request.

Technical data

Temperature range: -60°C up to +105°C

Flammability acc. to UL 94: V2

UV-stabilised

Part no.	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Unit	Net EUR/100 items at a purchase of		
							up to 1000	1001 - 5000	5001 - 10000
91052	TYB 23MX	92,0	2,4	16,0	80,0	1000	o. r.	o. r.	o. r.
91056	TY 232MX	203,0	2,4	50,0	80,0	1000	o. r.	o. r.	o. r.
91059	TY 234MX	356,0	2,4	102,0	80,0	1000	o. r.	o. r.	o. r.
91062	TYB 24MX	140,0	3,6	29,0	180,0	1000	o. r.	o. r.	o. r.
91065	TY 242MX	204,0	3,6	50,0	180,0	1000	o. r.	o. r.	o. r.
91068	TY 26MX	284,0	3,6	76,0	130,0	1000	o. r.	o. r.	o. r.
91071	TY 244MX	368,0	3,6	103,0	130,0	1000	o. r.	o. r.	o. r.
91074	TYB 25MX	186,0	4,8	45,0	220,0	1000	o. r.	o. r.	o. r.
91077	TY 253MX	295,0	4,8	78,0	220,0	1000	o. r.	o. r.	o. r.
91080	TY 28MX	361,0	4,8	102,0	220,0	1000	o. r.	o. r.	o. r.
91083	TY 272MX	223,0	6,9	50,0	540,0	500	o. r.	o. r.	o. r.
91086	TY 27MX	340,0	6,9	90,0	540,0	500	o. r.	o. r.	o. r.
91089	TY 29MX	771,0	6,9	229,0	540,0	500	o. r.	o. r.	o. r.

UV-stabilised - small package

Part no.	Type	Length mm	Width mm	Bundle Ø mm	Capacity N	Unit	Net EUR/100 items at a purchase of		
							up to 1000	1001 - 5000	5001 - 10000
97310	TY 5-23MX	92,0	2,4	16,0	80,0	100	o. r.	o. r.	o. r.
97311	TY 5-232MX	203,0	2,4	50,0	80,0	100	o. r.	o. r.	o. r.
97312	TY 5-234MX	356,0	2,4	102,0	80,0	100	o. r.	o. r.	o. r.
97313	TYB 5-24MX	140,0	3,6	29,0	180,0	100	o. r.	o. r.	o. r.
97314	TY 5-242MX	204,0	3,6	50,0	180,0	100	o. r.	o. r.	o. r.
97436	TY 5-26MX	284,0	3,6	76,0	130,0	100	o. r.	o. r.	o. r.
97437	TY 5-244MX	368,0	3,6	103,0	130,0	100	o. r.	o. r.	o. r.
93694	TY 5-25MX	186,0	4,8	45,0	220,0	100	o. r.	o. r.	o. r.
93695	TY 5-253MX	295,0	4,8	78,0	220,0	100	o. r.	o. r.	o. r.
93696	TY 5-28MX	361,0	4,8	102,0	220,0	100	o. r.	o. r.	o. r.
93697	TY 5-272MX	223,0	6,9	50,0	540,0	50	o. r.	o. r.	o. r.
93698	TY 5-27MX	340,0	6,9	90,0	540,0	50	o. r.	o. r.	o. r.
93699	TY 5-29MX	771,0	6,9	229,0	540,0	50	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request