

Carbon composition film preset potentiometers




Series 6

Type HA 06 / SM065

Ordering code no.: 00 006

Basic design: laminate base, plastic



Technical data

Rated resistance range	200 Ω - 1 MΩ	Limiting element voltage	50 V
Resistance tolerance	± 30 %	Mechanical travel	210° ± 10°
Law (resistance taper)	lin	Operating torque	0.5 - 3.5 Ncm
Rated dissipation	0.1 W / 50 °C	End stop torque	3.5 Ncm
Durability	100 cycles		