

Laserliner

AirCheck Clima



Digital hygrometer with ventilation recommendation to improve indoor climate

This digital hygrometer provides precise information on the ambient temperature and relative humidity. This practical device saves the minimum and maximum climate values. The user is warned of high air humidity and dryness. If the optimum humidity for people of 40 to 60 % is not maintained or the air is too dry, the indoor climate can be improved through the recommended ventilation. A well-balanced room climate has a positive influence on health, increases comfort levels, and helps avoid damage caused by moisture. The permanent time display and timer function are extremely useful, particularly when used in the kitchen. The LC display is easy to read. The fold-out stand/clip and integral magnets allow the device to be placed on tables, attached to objects, or fixed to metal surfaces. This hygrometer's attractive visual design makes it a winner!

- Precise measurement of relative humidity and ambient temperature and saves min./max. readings Measurements

TECHNICAL SPECIFICATIONS

MEASURED VARIABLE	Ambient temperature Humidity
FEATURES	Real-time clock MIN/MAX Humidity alarm Timer
MEASURING RANGE AMBIENT TEMPERATURE	-9,9°C ... 50°C
ACCURACY AMBIENT TEMPERATURE	± 1°C
MEASURING RANGE HUMIDITY (RELATIVE)	1% ... 99%
ACCURACY (ABSOLUTE) HUMIDITY (RELATIVE)	20% ... 80% (± 3%) <20% and >80% (± 5%)
POWER SOURCE	1 x 1.5V LR03 (AAA)
UNIT OF MEASUREMENT	°C (Celsius) % rH (relative humidity)
DIMENSIONS (W X H X D)	96 mm x 112 mm x 18 mm
WEIGHT	148 g (incl. batteries)



2x
AAA

