

Digital Wireless Camera System



DRC5040

Name		DRC5040
Art.no.		20135
EAN		8717809201355

Camera	
Operating Voltage	12/24V DC
Current consumption	<200mA (IR-LED OFF) <300mA (IR-LED ON)
Image sensor	CMOS
View Angle	110°
Pixels	1920x1080 Full HD
Minimal illumination	2 Lux
RF transmission distance	Up to 150 m
IP-Class	65

Miscellaneous	
Frequency	2.4G
Max. E.I.R.P	< 100mW

Monitor	
Input Voltage	12/24V DC
Standby Current	<120mA
Operating Current	<250mA
LCD display screen size	5 inch
Operating temperature	-10° - 50° C

Accessories	
Mounting set	1x
Monitor power cable	1x
Suction mount monitor	1x
User manual	1x
Mounting plate camera	1x



Digital Wireless Camera System
DRC5040

PRO^{ELECTRONICS®}**USER**